

# **RAM ION Meter**

**Highly Stable and Accurate Beta Gamma Detector** 

**Radiation Detection Division** 

**Health Physics** 



**The RAM ION** is a battery operated, auto ranging, portable ion chamber survey meter designed for highly stable and accurate measurement of dose rates and integrated dose of gamma, x-ray and beta radiation.

The meter covers a measuring range of 1  $\mu$ Sv/h - 500 mSv/h (0.1 mR/h to 50 R/h) in the dose rate mode, and 0.01  $\mu$ Sv -10 Sv (1uR to 999 R) in the integrated dose mode. The auto ranging meter utilizes a combination display consisting of a smoothed digital readout for minimum fluctuation and a two decade analog bar graph for fast response.

The **RAM ION** survey meter combines an ionization chamber vented to atmospheric pressure, and a micro-controller to offer optimal performances and special features. Furthermore it is a compact hand-held, lightweight, rugged meter, easy to use and maintain.

The **RAM ION** provides a very straightforward, fast and reliable method of collecting and storing monitoring data on site for later use. The **RAM ION** can read bar code labels that identify measurements location. The measurement's data combined with their locations, data and time are stored in a built in memory. The stored data records can be downloaded by the **RMV** (Rotem Meter View) software package.

The **RAM ION** is ideal for use in nuclear power plants, nuclear medicine, radiography and radiotherapy facilities, life science laboratories, nuclear research centers and in other industrial applications.

#### **Features**

- NDT safety providing accurate readings from 5 picosecond X-Ray pulses
- Wide measuring range of 1 µSv/hr to 500 mSv/hr (0.1 mR/hr to 50 R/hr)
- Built in memory to store data
- Compact, lightweight and easy-to-use, one hand operation
- Dose rate and accumulated dose measurement
- Display illumination
- Freeze mode to record the highest dose
- User programmable dose rate and accumulated dose alarms
- Remote PC communication
- Hot Spot detection

## **RAM ION Survey Meter**

### **Technical Data**

Accuracy ±10% of reading within measuring range

Gamma Energy Dependence (<sup>137</sup>Cs) Better than ± 20% at 20keV to 1.3MeV

Beta Energy Dependence Better that ± 20% from 200keV

6 MeV Energy moderating sleeve & Cover Available if required

Angular Dependence (137Cs) Less than ± 5% (for ±120° of front direction

Ion Chamber Volume 500 cc

Chamber Wall and Cover Thickness 300mg/cm<sup>2</sup> (tissue equivalent)

Window Thickness 7 mg/cm<sup>2</sup>

Response Time 2 sec. for readings above 1 mR/h

5 sec. for auto-ranging change, from Low Range to

High Range (2sec. +3 additional seconds for auto ranging delay)

Power Source (Built in automatic battery check)

meter: two 1.5V C-type Alkaline cells - 100 hours of continuous operation

Display DigiLog (3 digits and 2 decades of analog bar graph)
Data Logging 347 data records (1415 with extended memory)

Temperature Range Operation: -10°C to +50°C (15°F - 122°F)

Storage: -20°C to +60°C (-5°F - 140°F)

Humidity Range Up to 95% RH (non condensing)

Dimensions Width: 10cm (3.9"), length 25cm (9.8"), height 19cm (7.5")

Weight 1100g (2.4lb)
Casing High impact ABS

**NEW** USB connector providing both power and data transfer

# **Ordering Information**

BAK-1940	RAM ION DIGILOG <b>HR</b> (0.0) - μSv/h Radiation Detection Survey Meter
BAK-1920	RAM ION DIGILOG <b>HR</b> (0.00) - mR/h Radiation Detection Survey Meter
BAK-1950	RAM ION DIGILOG LR (0) - μSv/h Radiation Detection Survey Meter
BAK-1930	RAM ION DIGILOG LR (0.0) - mR/h Radiation Detection Survey Meter

BAK-2000 RAM ION DIGILOG X HR (0.0) - uSv/h Radiation Detection Survey Meter (new)
BAK-2005 RAM ION DIGILOG X HR (0.00) - mR/h Radiation Detection Survey Meter (new)

BAK-2010 RAM ION DIGILOG  $\times$  LR (0) -  $\mu$ Sv/h Radiation Detection Survey Meter BAK-1990 RAM ION DIGILOG  $\times$  LR (0.0) - mR/h Radiation Detection Survey Meter

HR = High Resolution – 1 or 2 decimal digits (depending on units of measurement)

LR = Low Resolution - no or 1 decimal digit (Depending on units..)

**X** = Used to measure pulsed X-rays. Instrument powers up in Dose Mode.

ROTEM INDUSTRIES reserves the right to change specifications without advance notice

30/01/2023







Mishor Yamin, D.N. Arava 8680600, Israel Tel. +972-8-6564780/1, Fax. +972-8-6573252

E-mail. sales@rotemi.co.il Web: www.rotem-radiation.co.il